



used for: D-SUB

POS.	A ±0.25	B ±0.15	C ±0.2	D ±0.2	Part NO.
9	31.11	25.00	16.92	16.92	320X12509X
15	39.51	33.28	25.25	25.25	320X12529X
25	53.35	47.04	39.06	39.06	320X10549X
37	69.65	63.50	55.42	55.42	320X12549X

- (d) (c)
- SPECIFICATION:
1. SHELL: TIN PLATED SHELL
  2. INSULATOR: PBT GLASS FIBRE REINFORCED UL 94 V0 (b) (d)
  3. CONTACTS: BRASS
  4. CONTACT PLATING: GOLD PLATED over NICKEL
  5. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND					General tolerance .X ±0.2 .XX ±0.15 .XXX ±0.05		 dim. in mm	scale: 2:1			
								material: SEE SPECIFICATION			
					2002	date	title:				
					drawn	30.04.	name				
	1 x e	Ä4765	28.05.2013	K.H.	appd.	30.04.	E.Mickenbecker				
	6 x d	Ä4520	30.10.2012	Lehm.	norm						
	2 x c	Ä4459	13.09.2012	Lehm.	d-old						
	1 x b	Ä2202	07.04.2005	HS							
	a	Original									
	rev.	description	date	name					dwg no:		DIN-A
								16K1A557		3	
								part no:		SEE TABLE	sh: 1/1

Directive 2002/95/EC RoHS compliant

DIN-A  
3  
sh: 1/1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[320X12529X](#)