








Fiber Optic Duplex LC
Adaptor Assembly
(Supplied with dust caps)
Dust cap should be removed
before mating with LC Plug



Notes:

- Material and Finish:
 - Receptacle Housing and Cover: Polyester (Black), UL94 V-0 or ABS, Nickel Plated, UL94 V-0
 - Panel Nut: Brass, Finish: Nickel Plated
 - Panel and Cover Gasket: Silicone, Color: White
 - Tether: Polycarbonate, Color: Black
- Duplex LC Adaptor Assembly:
 - Housing: Mod. PPO, UL94 V-0, Color: **SM Blue/MM Beige/APC SM Green**
 - Alignment Sleeves: SM Ceramic/MM Phosphor Bronze
 - Dust Cap: PP, Color: Neutral transparent
 - Operating Temperature: -40°C to +85°C
- Connector can be mounted to a maximum panel thickness of 3.2mm.
- IP67 rated when covered or fully mated with the appropriate mating connector
- Recommended Mounting Panel Nut torque is 20 to 25 lb-inch

Directive 2002/95/EC RoHS Compliant

Description	Plastic Version	Metallized Version
Single Mode (SM)	17-300820	17-300940
Multi Mode (MM)	17-300830	17-300950
APC Single Mode (APC SM)	17-300840	17-300960

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale:	Dim. in mm
	Name	Title	Approval Date	0 PLC ± 0.50	1 PLC ± 0.38		Autodesk Inventor	Material: See Notes Title: IP67 Industrial Duplex LC Receptacle + Cover Assembly Kit Plastic Version with bayonet on both sides
				2 PLC ± 0.25	3 PLC ± 0.10			
				ANGLES ± 3°				
	Rev. Changes Date Name			Draw. Sept. 28 Vincent Ke Appd. Sept. 28 J. Chaudry		Norm	Drawing No.: 17K1A335	
Rev. Changes Date Name			D-old		Part No.: SEE PART NUMBER TABLE			

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[17-300820](#) [17-300830](#)