




Notes:

1. Electrical:

- Meets EIA/TIA-568-B.2-10 Cat. 6A Channel Specification
- Connector Operating Temperature: -40° C to +85° C

2. Materials and Finish:

- Coupling Ring: Brass, Nickel Plated
- ⑥ - Plug Housing: Zinc Die-Cast, Nickel Plated
- Interfacial Seal: Silicon, Color: White
- Cable Gland: Brass, Nickel Plated
- Cable Gland Seal: NBR, Color: Black
- Cat.6A RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
- Cat.6A RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
- Cat.6A RJ45 Plug Contacts: Phosphor Bronze, Finish: 50 u" Gold min. over Nickel
- Cable: Cat.6A SFTP, 4 Pairs, AWG26, Stranded, Jacket Color: Black

RoHS Compliant

③ Patch Cord Length L	Part Number
1m ± 0.02m	17-180584
2m ± 0.03m	17-150794
3m ± 0.03m	17-180594
4m ± 0.04m	17-150804
5m ± 0.05m	17-150814
10m ± 0.10m	17-180604
20m ± 0.20m	17-180614

*Note: Special cable length and blue cable up to 20m are available please contact factory
Cable length > 20m cannot guarantee to meet TIA/EIA-568-C.2 Cat. 6A Specification.

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:			Tolerance Unless otherwise specified		 Autodesk Inventor	Scale: NTS	Dim. in meter
	Name	Title	Approval Date	0 PLC ±0.50	1 PLC ±0.38		Material: See Notes Cat. 6A RJ45 Ethernet Patch Cords IP67 Industrial to IP67 Industrial Hex 32, M28 Thread Metal Version	Drawing No.: 17K1A290 Part No.: SEE PART NUMBER TABLE
				2 PLC ±0.25	3 PLC ±0.10			
				ANGES	±3°			
		c	1 x c	Apr/15/2015	Vincent Ke	D-old		
	b	1 x b	Jun/23/2014	Vincent Ke				
	a	original						
	Rev.	Changes	Date	Name				

CONEC®

DIN
A3
Sheet
1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[17-150814](#) [17-150804](#) [17-150794](#)