






CONTACT PLATING	PART-NO.
SIGNAL CONTACTS GOLD FLASH over NICKEL	3H15W4SAM99A10X
SIGNAL CONTACTS 30µin HARD GOLD over 50µin NICKEL	3H15W4SCM99A10X



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: SEE TABLE
SOLDER CUP ACCEPTS CABLE AWG 22
- NO CONTACTS ON POS. A1 - A4
- CONNECTOR IS PART MARKED: **PART-NO. CONEC ABC**

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance			scale: 2:1 (5:1)					
								dim. in mm	material: SEE NOTES				
									date	name	title: D-SUB HD COMBINATION FEMALE 15W4S SOLDER CUP		
									drawn 13.03.2013	Liedmann			
									appd. 13.03.2013	Koch			
									norm				
									d-old				
											dwg no:		DIN-A3
					a	Original					13K1A4230		sh: 1
					rev.	description	date	name			part no: SEE TABLE		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[3H15W4SAM99A10X](#)