





NOTES:

- METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- NO CONTACTS ON POS. A1 - A3
- THREADED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
- COLLARS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3025W3PAM99A30X CONEC ABC



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance			scale: 2:1 (5:1)		
							material: see notes		
				dim. in mm		title: D-SUB COMBINATION MALE 25W3P SOLDER CUP with threaded insert			
DO NOT ALTER CAD DRAWING BY HAND				date		name		dwg no: 13K1A5000 DIN-A3 sh: 1	
				drawn 25.06.2015		Heinrich			
				appd. 25.06.2015		Lehmenkühler			
				norm					
				d-old				part no: 3025W3PAM99A30X	
a Original									
rev. description		date	name						

RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[3025W3PAM99A30X](#)