




NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACT ON POS. A1
5. CONNECTOR IS PART MARKED: 3021W1PAM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance				 dim. in mm		scale: 2:1 (5:1)											
																material: SEE NOTES											
										DO NOT ALTER CAD DRAWING BY HAND								date		name		title: D-SUB COMBINATION MALE 21W1P SOLDER CUP					
														drawn		27.05.13		Henneboel									
														appd.		27.05.13		Koch									
norm																											
				d-old				dwg no: 13K1A4333						DIN-A3													
a		Original												sh: 1													
rev.		description		date		name								part no: 3021W1PAM99A10X													

DIN-A3
sh: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[3021W1PAM99A10X](#)