








NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20

4. NO CONTACT ON POS. A1

5. CONNECTOR IS PART MARKED: 3021W1SAM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2:1 (5:1)	
								material: SEE NOTES	
					date	name	title: D-SUB COMBINATION FEMALE 21W1S SOLDER CUP		
					drawn 27.05.13	Henneboel			
					appd. 27.05.13	Koch			
					norm				
					d-old		dwg no:		DIN-A3
	a	Original					13K1A4332		sh: 1
	rev.	description	date	name			part no: 3021W1SAM99A10X		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[3021W1SAM99A10X](#)