









(5:1)



NOTES:

1. METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. NO CONTACTS ON POS. A1 - A2
5. CONNECTOR IS PART MARKED: 3017W2PAR99A10X CONEC ABC

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GMBH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Original		

tolerance	dim. in mm
date	name
drawn	14.09.15 Henneboel
appd.	14.09.15 Lehmenkühler
norm	
d-old	

scale:	2:1 (5:1)
material:	SEE NOTES
title:	D-SUB COMBINATION MALE 17W2P
dwg no:	13K1A5048
part no:	3017W2PAR99A10X
DIN-A3	sh: 1

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[3017W2PAR99A10X](#)