








NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 - A6
5. CONNECTOR IS PART MARKED: 3013W6SAM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)					
							material: see notes					
							date	name	title: D-SUB COMBINATON FEMALE 13W6S			
							drawn	29.10.14				Henneboel
							appd.	29.10.14				Schmidt
			norm			dwg no: 13K1A4798						
			d-old									
	a	Original				DIN-A3 sh: 1						
rev.	description	date				name	part no: 3013W6SAM99A10X					

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[3013W6SAM99A10X](#)