



USB Connector A Type PCB R/A SMT

SPECIFICATIONS

Materials

Insulator: thermoplastic, glass filled, UL 94V-0


Contacts: Phosphor bronze Plated: 10µ" gold plated SMD Plated: 120μ " tin plated Plastic: Nylon 6T
Shell: Copper alloy, tin plated


Electrical


Insulation Resistance: 1000 M Ω minimum Contact Resistance: 30 m Ω Max. initial

Dielectric Withstanding Voltage: 750V AC for one minute Current: 1.5 Ampere max. per contact at 30°C T-rise

Voltage: 30V AC (rms) Temperature: -55°C ~85°C







Order Information-----

33UBA RS1 - 04 5 W 1 1

1.Series No. 3.No. Of Contacts 04: 4 pin 33UBA

2.Terminal Version 4.Connector Type RS1: R/A SMT S: Female

5. Insulator Color W: White

7. Packaging 1: Packed in tray

6. Shield

1: W/O back shell 0: W/ back shell





File #: 127344

File #: LR97981

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

33UBARS1-04SW11