

D-SUB SHIELDED CAP

Metal design – Shielded




RoHS compliant


DESCRIPTION

- Shielded cap protecting against EMI/RFI
- Material: Steel tin plated
- Mounting style:
with Through-hole Ø .118" / 3.00 mm

SOCKET CONNECTOR



PLUG CONNECTOR



50-pos.= Dim. in (..)

No. of pos.	A-0.76	B1-0.25	B2+0.25	C	D-0.3
09	31.19	16.46	16.79	25.00 +0.12	6.12
15	39.52	24.79	25.12	33.30 +0.15	6.12
25	53.42	38.50	38.84	47.04 +0.13	5.99
37	69.70	54.96	55.30	63.50 +0.13	5.99
50	67.31	52.55	52.68	61.10 +0.14	5.99

ORDER DATA

SHIELDED CAP FOR SOCKET CONNECTOR		
No. of pos.	Design	Part Number
09	Metal /Through-hole Ø .118" / 3.00 mm	165X12969X
15	Metal /Through-hole Ø .118" / 3.00 mm	165X12979X
25	Metal /Through-hole Ø .118" / 3.00 mm	165X12989X
37	Metal /Through-hole Ø .118" / 3.00 mm	165X12999X
50	Metal /Through-hole Ø .118" / 3.00 mm	165X13009X

SHIELDED CAP FOR PLUG CONNECTOR		
No. of pos.	Design	Part Number
09	Metal /Through-hole Ø .118" / 3.00 mm	165X13129X
15	Metal /Through-hole Ø .118" / 3.00 mm	165X13139X
25	Metal /Through-hole Ø .118" / 3.00 mm	165X13149X
37	Metal /Through-hole Ø .118" / 3.00 mm	165X13159X
50	Metal /Through-hole Ø .118" / 3.00 mm	165X13169X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[165X13009X](#) [165X13159X](#) [165X13169X](#)