







(1:1)



* COMPLETELY TIGHTENED

NOTES:

1. MATERIALS:
HOOD: PBT GF UL94 V-0 BLACK
FRONTSEALING: SILICONE VMQ BLUE
SCREW: STAINLESS STEEL
O-RING: NBR BLACK
2. TEMPERATURE RANGE: -30°C TO +90°C
3. RECOMMENDED TORQUE FOR SCREW:
35Ncm (3.1 in.LB)
MAX. TORQUE: 68Ncm (6 in.LB)
4. SINGLE PACKED

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance ± 0,3 unless otherw. specified		 dim. in mm	scale: 1,5:1 (1:1)		
							material: SEE NOTES		
							title: WATER RESISTANT D-SUB HOOD (b) 15 POS. JACKSCREW 4-40UNC STAINLESS STEEL		
		date		name		dwg no: 15K1A1152 part no: (b) 15-004670			
		drawn 06.02.2014		Heinrich					
		appd. 06.02.2014		Huether					
		norm							
				d-old				DIN-A3 sh: 1	
b		Ä5090		06.02.2014		Heinrich			
a		Origin							
rev.		description		date		name			

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[15-004670](#)