




NOTES:

1. MATERIALS:

HOOD, GLAND, COMPR.-RING: ABS UL94 V-0 METALLIZED
 FRONTSEALING: SILICONE VMQ BLUE
 CABLE SEALING: NBR BLACK
 JACK-SCREW: STAINLESS STEEL
 O-RING: NBR BLACK
 CABLE STRAIN RELIEF: STEEL, NI-PLATED
 SCREWS: STEEL, NI-PLATED
 SHIELDING BRACKET: CU-ALLOY, NI-PLATED

2. TEMPERATURE RANGE: -30°C TO +80°C

3. RECOMMENDED TORQUE FOR SCREW:

35Ncm (3.1 in.LB)
 MAX. TORQUE: 68Ncm (6 in.LB)

4. SINGLE PACKED

* COMPLETELY TIGHTENED

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance ±0,3 unless otherw. specified			scale: 1,5:1 (1:1)	
					dim. in mm			material: SEE NOTES	
						date	name	title: WATER RESISTANT D-SUB HOOD SHIELDED 15 POS. SHORT SCREW 4-40UNC STAINLESS STEEL	
					drawn	07.02.2014	Heinrich		
					appd.	07.02.2014	Huether		
					norm				
					d-old		dwg no:		DIN- A3 sh: 1
	1 x b	Ä 5093	12.03.14	Heinrich			15K1A1443		
	a	Origin		part no:			15-004820		
	rev.	description	date	name					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[15-004820](#)