




- NOTES:**
- MATERIALS:**
HOOD, GLAND, COMPR.-RING: ABS UL94 V-0 METALLIZED
FRONTSEALING: SILICONE VMQ BLUE
CABLE SEALING: NBR BLACK
JACK-SCREW: STAINLESS STEEL
O-RING: NBR BLACK
CABLE STRAIN RELIEF: STEEL, NI-PLATED
SCREWS: STEEL, NI-PLATED
SHIELDING BRACKET: CU-ALLOY, NI-PLATED
 - TEMPERATURE RANGE:** -30°C TO +80°C
 - RECOMMENDED TORQUE FOR SCREW:**
35Ncm (3.1 in.LB)
MAX. TORQUE: 68Ncm (6 in.LB)
 - SINGLE PACKED**

* COMPLETELY TIGHTENED

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH						tolerance ±0,3 unless otherw. specified				scale: 1,5:1 (1:1)			
										dim. in mm		material: SEE NOTES	
								date		name		title: WATER RESISTANT D-SUB HOOD SHIELDED 25 POS. SHORT SCREW 4-40UNC STAINLESS STEEL	
								drawn 07.02.2014		Heinrich			
								appd. 07.02.2014		Huether			
				norm						dwg no: 15K1A1444 part no: 15-004830			
				d-old		15K1A1155							
1 x b		A 5093		12.03.14		Heinrich		DIN-A3					
a		Origin								sh: 1			
rev.		description		date		name							



Directive 2002/95/EC RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[15-004830](#)