

4



3

2

1

used for:

D-SUB



(b)

POS.	A	B	C	D max. cable ø	E	F	Part No. Single package
9	32.0	25.0	36.7	6.3	15.5	16.5	165X11319XE
15	40.0	33.3	38.2	8.0	15.5	16.5	165X11329XE
25	54.2	47.0	42.2	10.5	15.5	16.5	165X11339XE
37	70.6	63.5	47.2	11.5	15.5	16.5	165X11349XE

NOTES:

- HOOD + COVER: ABS UL 94 V-0, METALLIZED
- BLIND PLUG: ABS UL 94 V-0, METALLIZED
- CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
- COUNTERSUNK HEAD SCREW: STEEL; NICKEL PLATED
- JACKSCREW: BRASS; NICKEL PLATED

Directive 2002/95/EC
"RoHS"
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
1 x b	Ä 2607	21.11.2006	Lehmen	2006	date	
a	Origin			drawn	07.02.	Lehmenkühler
rev.	description	date	name	appd.	07.02.	Mickenbecker
				norm		
				d-old		

CONEC®

scale:	1:1	
material:	SEE NOTES	
title:	PLASTIC HOOD 9-37pos. WITH TOP AND SIDE CABLE EXIT with jack screws	
dwg no:	AutoCAD 2004	DIN-A
	16K1A1733	4
part no:	SEE TABLE	
		sh: 1/1

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[165X11319XE](#) [165X11329XE](#) [165X11339XE](#)