



1 x BLIND PLUG




1 x SPRING



1 x SLIDE LOCK



2 x SCREW



1 x CABLE STRAIN RELIEF



4 x SCREW

POS.	A	B	C	D max. cable $\phi$	Part No. Bulk package	Part No. Single package
9	32.0	25.0	36.7	6.3	165X11359X	165X11359XE
15	40.0	33.3	38.2	8.0	165X11369X	165X11369XE
25	54.2	47.0	42.2	10.5	165X11379X	165X11379XE
37	70.6	63.5	47.2	11.5	165X11389X	165X11389XE

MATERIAL:

HOOD: ABS UL 94 V-0; METALLIZED

BLIND PLUG: ABS UL 94 V-0; METALLIZED

SPRING: STAINLESS STEEL

SLIDE LOCK: STEEL; NICKEL PLATED

SCREWS: STEEL; NICKEL PLATED



CABLE STRAIN RELIEF: STEEL; NICKEL PLATED




THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.

OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
				2010	date	name
				drawn	14.04.	Lehmenkühler
				appd.	14.04.	Koch
				norm		
				d-old		
						
a	Origin					
rev.	description	date	name			



scale:	1:1
--------	-----

material:	SEE NOTES
-----------	-----------

title:
--------

## PLASTIC HOOD

9-37pos. with top and side cable exit  
with slide lock

dwg no:

AutoCAD 2006
--------------

DIN-A

16K1A2630

4

sh: 1/1

product no:	SEE TABLE
-------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

165X11369X