

4


3

2

1

used for:

D-SUB



No. of pos.	A	B	C	D	E	ØF	Part-N0.	
9	32.9	25.0	39.5	41.8	16.3	11.0	165X13369X	600X10009XS
15	41.2	33.3	45.5	47.8	16.3	11.0	165X13379X	600X10015XS
25	54.9	47.0	52.5	54.8	16.3	12.0	165X13389X	600X10025XS
37	71.4	63.5	55.0	57.8	18.7	15.0	165X13399X	
50	69.0	61.1	55.0	57.8	19.5	14.0	165X13409X	

(b)

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACION * APPROVAL	

TECHNICAL DATA:

MATERIAL: PBT UL 94 V-0



COLOUR: BLACK


TEMPERATURE RANGE: -55°C to + 140°C

(b)

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance			
				2002	date	name	
				drawn	08.07.	Parei	
				appd.	08.07.	E. Mickenbecker	
				norm			
				d-old			
2 x b	Ä5307	25.08.2014	E.Mick.				
a	Original						
rev.	description	date	name				



scale: 1:1
material: SEE TECHNICAL DATA

title:
PLASTIC HOOD
9-50pos.
with straight cable exit

dwg no: AutoCAD 2000 DIN-A
16K1A707 4
sh: 1/1

part no: SEE TABLE

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

165X13379X