






NOTES:

1. METAL SHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. RUBBER-GASKET: TPE
5. CONNECTOR IS PART MARKED: PART NO CONEC ABC



(b)

No. of pos.	A	B	C	D	Part-No.
9	30,88 +0,31/-0,45	16,84 +0,2/-0,05	24,99 +0,13/-0,12	6,00 +0,12/-0,18	4STD09PCM99A10X
15	39,22 +0,3/-0,46	25,17 +0,2/-0,05	33,32 +0,13/-0,12	6,00 +0,12/-0,18	4STD15PCM99A10X
25	53,09 +0,33/-0,43	38,86 +0,23/-0,02	47,04 ± 0,13	6,00 -0,3	4STD25PCM99A10X
37	69,39 +0,31/-0,45	55,30 +0,25/-0,02	63,50 ± 0,13	6,00 -0,3	4STD37PCM99A10X

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			
DO NOT ALTER CAD DRAWING BY HAND			
1 x c	Ä 3495	10.11.09	Petker
1 x b	Ä 2179	07.03.05	Lehm.
a	Origin		
rev.	description	date	name

tolerance	dim. in mm	scale:	2:1 (5:1)
		material:	SEE NOTES
		title:	D-SUB MALE SOLDER CUP 9-37pos. for installation into water resistant hood
		dwg no:	Inventor 10 (C) DIN-A3
			sh: 1
		part no:	SEE TABLE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[4STD09PCM99A10X](#)