








NOTES:

1. METALSHELLS: STEEL; min. 320 μ " TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. HIGH POWER CONTACTS 20A: COPPER ALLOY
4. PLATING: min. 30 μ " HARD GOLD OVER min. 50 μ " NICKEL
5. SOLDER CUP ACCEPTS CABLE AWG 12-14
6. = CRITICAL DIMENSION: SPC

**Directive 2002/95/EC
"RoHS"
Compliant**

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONE GmbH
DO NOT ALTER CAD DRAWING BY HAND

[illegible]

tolerance		
	2001	name
	drawn	Parej
	appd.	Schrader
	norm	
	d-old	



scale:	2:1 (5:1)
material:	SEE NOTES
title:	
D-SUB COMBINATION FEMALE 5W5S	
dwg no:	AutoCAD 2000
	DIN-A
	3
	sh: 1/1
part no: 3005W5SXX42A10X	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[3005W5SXX42A10X](#)