





# SPECIFICATION

Current Rating:7A AC/DC  
Voltage Rating:250V AC/DC  
Withstanding Voltage:1500V AC/Minute  
Contact Resistance:20 Milliohms Max.  
Insulation Resistance:1000 Megaohms Min.  
Temperature Range:-25°C~+85°C  
Insulator:PA66(UL94V-2)  
Pin:Brass,Tin Plated  
RoHS Compliant



Recommended P.C.B. Layout



**4UCON** 元化興業股份有限公司  
4UCON TECHNOLOGY INC.

DRAWING No.

21596

APPROVED BY

MEI

CHECKED BY

HZF

DRAWING BY

CYP

UNLESS OTHERWISE  
SPECIFIED  
TOLERANCES ARE  
.X. ±0.30  
.X ±0.25  
.XX ±0.20  
.XXX ±0.05  
ANG. ±1°


SCALE

NONE

REV.

A0

UNIT  
mm



NO. REV.

A0 NEW RELEASE

REVISIONS

CHK

DATE

05/08/2018

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[PRT-15700](#)