



REV	ECRN	DATE
1	NEW PRODUCTION	20190528



P/N	L(mm)	T(mm)	Cutting line size(mm)	朋联料号
	300	10	300	9.00ACCA2532.003R
	800	10	800	9.00ACCA2532.008R
	2000	30	2000	9.00ACCA2532.020R

NOTES:
 1.ELECTRICAL TEST:100%OPEN,SHORT&MIS WIRE TEST.
 2.CONTACT RESISTANCE:2 ohm,
 3.INSULATOR RESISTANCE:5M ohm.
 4.HIGH VOLTAGE:DC 300V 0.01sec.
 5.MUST BE ROHS COMPLIANT.



接线表

P1	P2
1 RED	A4+A9+B4+B9 VCC
2 WHITE	A7 D-
3 GREEN	A6 D+
4 DRAIN	A1 A12 B1 B12 GND
SHELL BRAID	SHELL

	I.000001.0400R	TIE	L=100mm COLOR BLACK	1	PCS
⑥	J.000008.0500R	TIN WIRE	TIN WIRE OD:0.8MM	2.5	G
⑤	C.085P01.0200R	MOLDING	TPE 85A BLACK	10	G
④	C.0000P00.0000R	MOLDING	PE	3	G
③		CONNECTOR	USB 2.0 TYPE C/M GOLDEN PLATED SHELL NICKEL PLASTIC:BLACK 56.0KΩ	1	PCS
②	B.01004M.0N01R	CONNECTOR	USB A/M 4P PIN GOLDEN PLATED SHELL NICKEL PLASTIC: WHITE Double sided insert	1	PCS
①		CABLE	NO UL32AWG (11/0.06TS)*2C+23AWG (98/0.0.06TS)*1C+D (41/0.08TS)*1C+AL+B(16/4/0.08TS) JACKET TPE 65A BLACK OD:2.8MM	1	PCS
NO.	PART NO	ITEM	DESCRIPTION	Q'TY	UNIT

RoHS COMPLIANT



朋联电子有限公司

DongGuan PengLian Electronics Co.,Ltd
 TEL:076938835098/38835095 FAX:076938835091

DRAWN BY		
CHECKED BY		
APPROVED BY		

比例: FREE	TITLE: USB 2.0 A/M TO USB 2.0 TYPE C
單位: mm	SUPPLIER`S ITEM: 9.00ACCA2532.XXXR
	CUSTOMER: SPARK FUN
	CUSTOMER`S ITEM:
DRAWING NO. ACCA-2532	DATE 2019.05.28

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[CAB-15424](#) [CAB-15425](#) [CAB-15426](#)