




REV	ECRN	DATE
1	NEW PRODUCTION	20190515

P1



P2



PIN WIRING

P1

P2

A4, B4, A9, B9	RED(24AWG)	A4, B4, A9, B9
A1, B1, A12, B12	DRAIN*2	A1, B1, A12, B12
A5	BLUE(32AWG)	A5
B5	YELLOW(32AWG)	B5
A6	GREEN	A6
A7	WHITE	A7
A2	YELLOW(RED MYLAR)	A2
A3	BLUE(RED MYLAR)	A3
B11	YELLOW(GREEN MYLAR)	B11
B10	BLUE(GREEN MYLAR)	B10
B2	YELLOW(YELLOW MYLAR)	B2
B3	BLUE(YELLOW MYLAR)	B3
A11	YELLOW(LUCENCY MYLAR)	A11
A10	BLUE(LUCENCY MYLAR)	A10
A8	RED(32AWG)	A8
B8	BLACK(32AWG)	B8
SHELL	BRAID	SHELL

- NOTES:
- 1.ELECTRICAL TEST:100%OPEN,SHORT&MIS WIRE TEST.
 - 2.CONTACT RESISTANCE:2 ohm,
 - 3.INSULATOR RESISTANCE:10 ohm.
 - 4.HIGH VOLTAGE:DC 300V 0.01sec.
 - 5.MUST BE ROHS COMPLIANT.

⑦	J.000008.0500R	TIN WIRE	TIN WIRE OD:0.8MM	2.5	G
⑥	G.035523.3100R	SCREW	M3 NUT	2	PCS
⑤	C.000000.0000R	MOLDING	PE	4.5	G
④	C.045P06.0100R	MOLDING	PVC 45P BLACK	11.5	G
③		CONNECTOR	USB 3.0 TYPE C/M Black rubber core iron shell plating nickel	1	PCS
②		CONNECTOR	USB 3.0 TYPE C/F Black rubber core iron shell plating nickel	1	PCS
①		CABLE	(32AWG*1P+D+AL+MY)*1C+(32AWG*1P+AL+MY)*4C+30AWG*1P+24AWG*1C+32AWG*2C +AL+D+B JACKET PVC 60P BLACK OD=4.3±0.1mm L=200MM	1	PCS
NO.	PART NO	ITEM	DESCRIPTION	Q'TY	UNIT

RoHS COMPLIANT



朋联电子有限公司

DongGuan PengLian Electronics Co.,Ltd
TEL:076938835098/38835095 FAX:076938835091

DRAWN BY	袁小政	20190515
CHECKED BY		
APPROVED BY		

比例: FREE	TITLE: USB 3.0 TYPE C/F TO USB 3.0 TYPE C/F
单位: mm	SUPPLIER`S ITEM: 9.00ACCA2517.000R
	CUSTOMER: SPARK FUN
	CUSTOMER`S ITEM:
DRAWING NO. ACCA-2517	DATE 2019.05.15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[CAB-15455](#)