


Datasheet of Hanging Load Cell



Comprehensive Accuracy	(%F.S)	0.05
Load (Capacity)	(kg)	10
Output Sensitivity	(mV/V)	1.0±0.1
Zero Output	(mV/V)	±0.1
Nonlinearity	(%F.S)	0.05
Repeatability	(%F.S)	0.05
Hysteresis	(%F.S)	0.05
Creep	(%F.S/3 min)	0.05
Zero Drift	(%F.S/1 min)	0.05
Temp. Effect on Zero	(%F.S/10℃)	0.2
Temp. Effect on Span	(%F.S/10℃)	<0.15
Input Resistance	(Ω)	1000±50
Output Resistance	(Ω)	1000±50
Insulation Resistance	(MΩ 100VDC)	≥2000
Excitation Voltage	(V)	3-12
Operating Temperature	(℃)	-10 to +50
Ultimate Overload	(%F.S)	150

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[SEN-21669](#)