


SPECIFICATION

Current Rating: 1A AC,DC
Voltage Rating: 100V AC,DC
Temperature Range: -25°C ~ +85°C
Contact Resistance: 20 Milliohms Max.
Insulation Resistance: 1000 Megaohms Min.
Withstanding Voltage: 800V AC/Minute
Insulator: PA66+30%GF, UL94V-0
Pin: Brass,
Underplated: Nickel
Whole Tin Plated
RoHS Compliant



Poles	Dim.A	Dim.B
2	2.00	6.00
3	4.00	8.00
4	6.00	10.00
5	8.00	12.00
6	10.00	14.00
7	12.00	16.00
8	14.00	18.00
9	16.00	20.00
10	18.00	22.00
11	20.00	24.00
12	22.00	26.00
13	24.00	28.00
14	26.00	30.00
15	28.00	32.00
16	30.00	34.00

4UCON 元化興業股份有限公司
4UCON TECHNOLOGY INC.

DRAWING No.

01548

SCALE

NONE

APPROVED BY

MEI

CHECKED BY

HZF

DRAWING BY


PEGA

REV.

B0

UNLESS OTHERWISE
SPECIFIED

TOLERANCES ARE
~10 ±0.15
20~30 ±0.30
30~ ±0.50
ANG ±2°

UNIT
mm

NO. REV.

B0 NEW RELEASE

REVISIONS

HZF

12/05/2006

CHK

DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[PRT-09749](#)