



Specifications:

	Item	Parameters
Module	Module size	192 x 192mm
	Pixel pitch	3mm
	Pixel density	111,111 pixels/ sqm
	Pixel configuration	1R1G1B
	Package mode	SMD2121
	Pixel resolution	64 pixels (W) x 64 (H) pixels
	Max power consumption	18W
	Module thickness	14.66mm (without magnet)
		26.55mm (with magnet)
	Weight	0.31kg
	Drive type	Constant drive
	Scan mode	1/ 16 scan
	Port type	HUB75-A
	Brightness of white balance	≥ 1,200cd/sqm
Cabinet	Dimension	576 x 576mm
	Quantity of module	9pcs
	Power supply	5V 60A x 1pcs
	Thermal discharge	fan x 0 pcs
	Pixel per cabinet	192 x 192 pixels
	Best viewing distance	3-20m
	Best viewing angles	(H/V): 160 120
	Temperature	Storage: -35 - +85℃
		Working: -20 - +50℃
	Operation humidity	10% - 95%
	Thickness	65mm
Power	Working voltage	AC 220V 0%
	Average power consumption	180W/ sqm
	Max power consumption	≤ 360W/ sqm
	Current	≤ 20mA (single LED)
Main technical parameter	Driving device	Constant current driving IC
	Refresh rate	≥ 1,920Hz
	Grey scale	256 levels of each color (RGB)
	Colors	16.7m colors
	MTBF	≥ 100K hours
	Power switch	Automatic switch
	Display mode	800 x 600/ 1,024 x 768

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[COM-14824](#)