


注:

- 裁线时线皮口需切齐不可歪斜.
- 注意IDC连接器压合后的方向.
- K=K出口纸箱包装, 每一层用隔板隔开.
- 电气特性符合以下要求:
耐电压:300V, 导通阻抗:3欧, 绝缘
阻抗:10M欧

接点图:

P1	1	2	3	X	X	X	10	11	12
P2	1	2	3	X	X	X	10	11	12

1	PUYER E485433 PY4201-10B01W01 2PCS	OPERATION		DRAW	DATE 2017/05/10	SCALE	FIT	Dongguan Penglian Electronics Co., Ltd.	
		X.	±0.20			UNIT	mm		
2	PUYER E350147 UL2678 30AWG PH=0.635mm 10C 灰色红边排线 L=160mm 1PCS	X. X	±0.15	CHECK	DATE	SIZE	A4	Part Number	SP-06 1.27 10p
		X. XX	±0.10	APPROVE	DATE	SHEET	1/1		
		ANGLES	±2°			PROJ.			
		DIM.	TOL						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[CAB-15364](#)