

SPECIFICATION

Name	DC12V10M	PART NO.	N/A
TYPE	N/A	REV	A

Storage Temperature: -20 – 80°C

Operating Temperature: -20 - 60°C

Working Temperature: ≤50°C

Parameter	Symbol	Test Condition	Min	Typ.	Max	Unit
Operating Voltage	VDD	Normal	11	12	13	V
Operating Power	IOUT	Normal	2	5	9	W
EL Output Voltage	VEL	Normal	70	90	110	V
EL Output Frequency	VFEL	Normal	0.8K	2K	3.5K	Hz

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[COM-10469](#)