





SPECIFICATIONS

Voltage Rating: 300VAC
 Current Rating: 8 Amps/Way Max
 Insulation Resistance: 5000 Megohms/1000V
 Withstanding Voltage: 1500VAC(1min) Test Time=60sec/1pcs
 Wire Range: 14–26AWG
 Torque: 4kgf.cm/M2.5
 Operating Temperature: -30°C To +105°C
 Soldering Reliability:
 Test Temperature=250°C±10°C/5 Seconds Max
 Contact(Metal Housing): Brass Stamping
 Terminal Screw: Steel Galvanized And Chromatized
 Wire Guard: Copper Alloy
 Surface Of Solder Tail: Tin Plated
 Insulator Body(Housing): Polyamide(Glass Filled)(UL94V-0)



4UCON元化興業股份有限公司
4UCON TECHNOLOGY INC.

DRAWING No.

05345

APPROVED BY

MEI

CHECKED BY

HZF

DRAWING BY

PEGA

UNLESS OTHERWISE
SPECIFIED
TOLERANCES ARE
X. ± 0.50
.X ± 0.30
.XX ± 0.20
ANG. $\pm 1^\circ$

UNIT	mm
------	----



SCALE

NONE

REV.

A1

NO.	REV.
-----	------

REVISIONS

CHK

DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[PRT-08433](#)