



#### NOTES:

1. ELECTRICAL TEST: 100% OPEN, SHORT & MIS WIRE TEST.
2. CONTACT RESISTANCE: 2 ohm,
3. INSULATOR RESISTANCE: 10M ohm.
4. HIGH VOLTAGE: DC 300V 0.01sec.
5. MUST BE ROHS COMPLIANT.

#### PIN WIRING

P1		P2
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	4
5		5
SHELL	DRAIN WIRE	SHELL

#### BOM

PL-EF-04

5	MOLDING	PVC 45P BLACK	1PCS
4	MOLDING	PE	13.6g/PCS
3	CONNECTOR	MICRO USB-A 5P PIN GOLDDED PLATED SHELL NICKEL PLASTIC: BLACK	1SET
2	CONNECTOR	USB A/F 4P PIN GOLDDED PLATED SHELL NICKEL PLASTIC: WHITE	1SET
1	CABLE	28AWG (7/0.12TC) *4C (RED, WHITE, GREEN, BLACK) +D (7/0.12TC) +B (32/0.10TC) +AL JACKET PVC 60P BLACK OD=4.0 ± 0.1mm L=100MM	1PCS

NO.	NAME	SPECIFICATION	Q' TY
-----	------	---------------	-------



朋联电子有限公司

DongGuan PengLian Electronics Co., Ltd

TEL: 076938835098/38835095 FAX: 076938835091

TITLE	USB A/F TO MICRO USB-A 5P				
	CUSTOMER				
	CUSTOMER'S ITEM				
SCALE	1: 1	DRAWN BY	赵忠诚	DATE	2012-09-17
UNIT	mm	CHECKED BY		DRAWING NO.	
REV.	A	APPROVED BY			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[CAB-11604](#)