





SPECIFICATIONS

Current Rating: 1.5 Amp
 Insulator Resistance: 1000 Megohms Min.
 Contact Resistance: 20 Milliohms Max.
 Dielectric Withstanding: AC 500V/Minute
 Operating Temperature: -40°C To +105°C
 Contact: Phosphor Bronze, Gold Flash Over All
 Insulator: Polyester, PA6T+30%GF, UL 94V-0



Recommended P.C.Board Hole Layout



4UCON 元化興業股份有限公司
 4UCON TECHNOLOGY INC.

DRAWING No.

00286

SCALE

NONE

APPROVED BY

MEI

CHECKED BY

BECKY

DRAWING BY

HZF

REV.

B1


UNLESS OTHERWISE
 SPECIFIED
 TOLERANCES ARE

.X ± 0.38

.XX ± 0.25

.XXX ± 0.12

UNIT
 mm



NO. REV.

REVISIONS

CHK

DATE

B1

Modify PA66 → PA6T

SHIN

02/06/2006

B0

NEW RELEASE

BECKY

09/30/2005

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[PRT-08272](#)