






REVISION		
REV.	DESCRIPTION	DATE
1.0	NEW ISSUE	12/29-15



M0501649(内插)
M0501649(外插)



- ELECTRICAL CHARACTER:**
- 100% OPEN&SHORT TESTING
 - WITHSTANDING VOLTAGE:DC 300V 0.1Sec
 - INSULATION RESISTANCE:20M Ohms(Min)
 - CONDUCTIVE RESISTANCE:1.0 Ohms(Max)

<u>CONN.#1</u>		<u>CONN.#2</u>	
1	_____	1	_____
2	_____	2	_____
3	_____	3	_____
4	_____	5	_____
5	_____	6	_____
6	_____	7	_____
7	_____	8	_____
8	_____	9	_____
9	_____	10	_____
SHELL	_____	SHELL	_____

7	OVERMOLD	3.5g	YL0103011	PVC 25P BLUE UL94V-0
6	OVERMOLD	3.5g	YL0103014	PVC 45P BLUE UL94V-0
5	INNERMOLD	1.7g	YL0103013	PE LOW DENSITY
4	CONN#2	1	YL0102234	USB3.0 MicroB 超薄 铜壳镀镍 端子镀金1u
3	CONN#1	1	YL0102231	USB 3.0 AF 短体 镀金1u
2	CABLE	1	QT0601005	电子线 7/0.12TC L=0.03M
1	CABLE	9	QT0601011	电子线 7/0.12TC L=0.023M
NO.	DESCRIPTION	QTY.	PART NO.	MATERIAL
			J	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AAEON:](#)

[EP-CBUSBAFMBLT1](#)