



RoHS Compliant

REV	DESCRIPTION	DATE
A0	INITIAL RELEASE	2016-12-29



PIN ASSIGNMENTS



PIN ASSIGNMENTS

NOTES:

1. ELECTRICAL TEST: 100% OPEN, SHORT & MIS WIRE TEST.
2. CONTACT RESISTANCE: 10 ohm,
3. INSULATOR RESISTANCE: 5M ohm.
4. HIGH VOLTAGE: DC 300V 0.01sec.
5. MUST BE ROHS COMPLIANT.

P1	COLOR	P2	P3
1	YELLOW	1	
2	BLUE	2	
3	ORANGE	3	
4	BROWN	4	
5	RED	5	
6	WHITE	6	
7	GREEN	7	
8	BLACK	8	28AWG BLACK 3
		9	28AWG RED 2
		10	28AWG WHITE 1

14	WIRE	UL1571 28AWG(7/0.12TC)OD:0.9mm RED/BLACK/WHITE	3 PCS
13	TUBE	OD1.5*10mm Black Heat Shrink TUBE	1 PCS
12	TUBE	OD8.0*15mm Black Heat Shrink TUBE	1 PCS
11	MOLDING	PVC 45P BLACK	11.5G
10	MOLDING	PE	6.50G
9	TIN WIRE	TIN WIRE OD:0.8MM	10.5G
8	SCREW	M3 OD3.0*Length 14mm SCREW	2 PCS
7	TIE	CABLE TIES COLOR:WHITE	1 PCS
6	TERMINAL	JST :SSH-003T-PO.2-H	10 PCS
5	HOUSING	JST:SHR-10V-S-B HOUSING:WHITE	1 PCS
4	TERMINAL	DUPONT:2.54 GOLD-PLATING	9 PCS
3	HOUSING	DUPONR:2.54-1*3P HOUSING:BLACK KEY10	1 PCS
2	CONNECTOR	双层USB A/F*2 PIN GOLD PLATED SHELL NICKEL PLASTIC:WHITE	1 PCS
1	CABLE	(12/0.11BC)*8C+AC+B(64/0.09TC) OD:5.2mm	1 PCS
序号	材料名称	规格描述	用量

图号 (DWG NO)	单位(UNIT) MM	品名 (ITEM NO)	USB A/F TO JST PH1.0 10P HSG
版次 (REV)	比例(SCALE)任意		
页次 (PAGE)	1/1	料号 (PART NO)	
设计 (DESIGN)	未注公差 TOLERANCE UNSPECIFIED		
审核 (CHECKED)	X.X ±0.25 X.XX ±0.15 X.XXX ±0.05		
核准 (APPROVED)	X' ±.5" X.X' ±.2"		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AAEON:](#)

[EP-CBUSB10PFL01](#)