

Coaxial Cable Connector 16_N-50-3-103/133_N

Description

Right angle cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0381 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU, RoHS	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00006846
Catalogue drawing	DOU-00006848
Assembly instruction	DOC-0000180775

Ordering Information

Single package	16_N-50-3-103/133_NE
----------------	----------------------

Additional Information

Suitable cables	RG_58_C/U, RG_223_/U, G_03233_D, ENVIROFLEX_400
-----------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

16_N-50-3-103/133_NE