

Coaxial Cable Connector 14_BMA-50-2-3/199_N

Description

Straight bulkhead cable plug

Interface standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0035 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU, RoHS	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Fastening nut	Stainless Steel	
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	Nickel Plating

Related Documents

Catalogue drawing	DCA-00010008
Assembly instruction	DOC-0000184996
Mounting hole	DOU-00008972

Ordering Information

Single package	14_BMA-50-2-3/199_NE
----------------	----------------------

Additional Information

Suitable cables	RG_316_/U, RG_188_A/U, RG_174_/U
-----------------	----------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[14_BMA-50-2-3/199_NE](#)