

## Coaxial Cable Connector 11\_BNC-50-2-20/103\_N

### Description

Straight cable plug

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

|                          |             |
|--------------------------|-------------|
| Impedance                | 50 $\Omega$ |
| Interface frequency max. | 4 GHz       |

#### Mechanical Data

|                |           |
|----------------|-----------|
| Centre contact | soldered  |
| Outer contact  | soldered  |
| Weight         | 0.0096 kg |

#### Environmental Data

|                                                      |                  |
|------------------------------------------------------|------------------|
| Operating temperature                                | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

| Piece Parts    | Material              | Surface Plating                   |
|----------------|-----------------------|-----------------------------------|
| Centre contact | Brass                 | Gold Plating (Nickel underplated) |
| Outer contact  | Brass                 | Silver Plating                    |
| Body           | Brass                 | Silver Plating                    |
| Insulator      | PFA / PTFE            |                                   |
| Coupling nut   | Brass                 | SUCOPLATE (R) Plating             |
| Gasket         | VMQ (Silicone rubber) |                                   |

### Related Documents

|                      |                |
|----------------------|----------------|
| Outline drawing      | DOU-00007339   |
| Catalogue drawing    | DOU-00007341   |
| Assembly instruction | DOC-0000238074 |

### Ordering Information

|                |                       |
|----------------|-----------------------|
| Single package | 11_BNC-50-2-20/103_NE |
|----------------|-----------------------|

### Additional Information

|                 |                           |
|-----------------|---------------------------|
| Suitable cables | EZ_86_TP_M17, SUCOFORM_86 |
|-----------------|---------------------------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[11\\_BNC-50-2-20/103\\_NE](#)