

## Coaxial Cable Connector 11\_C-50-7-6/133\_N

### Description

Straight cable plug

Interface standards

IEC 60169-7\_MIL-STD-348A/302



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0463 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

### Related Documents

Outline drawing	DOU-00007304
Catalogue drawing	DCA-00007306
Assembly instruction	DOC-0000179854

### Ordering Information

Single package	11_C-50-7-6/133_NE
----------------	--------------------

### Additional Information

Suitable cables	RG_214_/U, G_03232_D-01, GX_07272_D
-----------------	-------------------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

11\_C-50-7-6/133\_NE