

## Coaxial Cable Connector 11\_MMBX-50-1-1/111\_N

### Description

Straight cable plug

Interface standards  
SUHNER-MMBX



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0011 kg

#### Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

### Related Documents

Outline drawing	DOU-00007061
Catalogue drawing	DOU-00007063
Assembly instruction	DOC-0000181037

### Ordering Information

Single package	11_MMBX-50-1-1/111_NE
----------------	-----------------------

### Additional Information

Suitable cables	ENVIROFLEX_178, RG_178_B/U, RG_196_A/U
-----------------	--

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11\\_MMBX-50-1-1/111\\_NE](#)