

## Coaxial Cable Connector 11\_MM CX-50-1-2/111\_O

### Description

Straight cable plug

Interface standards  
SUHNER-MM CX



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	6 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0009 kg

#### Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	Gold Plating (without Nickel underplating)

### Related Documents

Outline drawing	DOU-00006166
Catalogue drawing	DOU-00006168
Assembly instruction	DOC-0000179110

### Ordering Information

Single package	11_MM CX-50-1-2/111_OE
Bulk 100 pcs package	11_MM CX-50-1-2/111_OH

### Additional Information

Suitable cables	K_01152-07
-----------------	------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[11\\_MMCX-50-1-2/111\\_OH](#)