

Coaxial Cable Connector 11_MM CX-50-2-1/111_O

Description

Straight cable plug

Interface standards
SUHNER-MM CX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	crimped
Outer contact	soldered
Weight	0.0004 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DOU-00006168
Assembly instruction	DOC-0000180170

Ordering Information

Bulk 100 pcs package	11_MM CX-50-2-1/111_OH
Single package	11_MM CX-50-2-1/111_OE

Additional Information

Suitable cables	EZ_86_TP_M17
-----------------	--------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[11_MMCX-50-2-1/111_OE](#)