

Coaxial Cable Connector 11_NEX10-50-3-X1/003_-

Description

Straight cable plug

Interface standards
NEX10



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	20 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00327566
Catalogue drawing	DCA-00343823
Assembly instruction	DOC-0000764175

Ordering Information

Bulk 100 pcs package	11_NEX10-50-3-X1/003_-H
----------------------	-------------------------

Additional Information

Suitable cables	SUCOFORM_141_CU_FEP
-----------------	---------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[11_NEX10-50-3-X1/003_-H](#)