Data Sheet

HUBER+SUHNER

Coaxial Cable Connector
11_SHV-50-4-10/133_N

Description

Straight cable plug

Interface standards
IEC 60498_MIL-STD-348A/314

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	0.3 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0223 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00069091
Catalogue drawing	DOU-00006114
Assembly instruction	DOC-0000179083

Ordering Information

Single package	11_SHV-50-4-10/133_NE

Additional Information

Suitable cables	RG_59_B/U, GX_04273

Remarks

High voltage connector Working voltage (at sea level) 3.5 kV rms, 50Hz (depending on cable)

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:
11_SHV-50-4-10/133_NE