

Coaxial Cable Connector 11_SMA-50-3-42/-33_N

Description

Straight cable plug

Interface standards

SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	26.5 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0033 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact		
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00006525
Catalogue drawing	DOU-00006518
Assembly instruction	DOC-0000179294

Ordering Information

Single package	11_SMA-50-3-42/-33_NE
----------------	-----------------------

Additional Information

Suitable cables	EZ_141_TP_M17
-----------------	---------------

Remarks

EI. Optimized for cable RG 58 C/U

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_SMA-50-3-42/-33_NE](#)