

Coaxial Cable Connector 11_SMA-50-3-56/199_N

Description

Straight cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0039 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DOU-00006088
Assembly instruction	DOC-0000179078

Ordering Information

Bulk 100 pcs package	11_SMA-50-3-56/199_NH
Single package	11_SMA-50-3-56/199_NE

Additional Information

Suitable cables	RG_223_/U, RG_142_B/U, RG_400_/U, RADOX_RF_400, ENVIROFLEX_142
-----------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[11_SMA-50-3-56/199_NE](#)