

## Coaxial Cable Connector 11\_SMA-R50-3-238/133\_N

### Description

Straight cable plug

Interface standards  
SUHNER-SMA-R50



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.003 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00178105
Catalogue drawing	DCA-00180987
Assembly instruction	DOC-0000360525

### Ordering Information

Bulk 500 pcs package	11_SMA-R50-3-238/133_NP
Single package	11_SMA-R50-3-238/133_NE

### Additional Information

Suitable cables	ENVIROFLEX_400, G_03262_D, RADOX_RF_400
-----------------	---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11\\_SMA-R50-3-238/133\\_NP](#)