

Coaxial Cable Connector 11_UHF-0-3-18/033_-

Description

Straight cable plug

Interface standards
IEC 60169-12



Technical Data

Electrical Data

Impedance	other Ω
Interface frequency max.	0.2 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0206 kg

Environmental Data

Operating temperature	-55 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PSU (Polysulfone)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00181573
Catalogue drawing	DCA-00045041
Assembly instruction	DOC-0000201061

Ordering Information

Single package	11_UHF-0-3-18/033_-E
----------------	----------------------

Additional Information

Suitable cables	RG_223_/U, RG_142_B/U
-----------------	-----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

11_UHF-0-3-18/033_-E