

## Coaxial Cable Connector 11\_UHF-0-7-18/033\_-

### Description

Straight cable plug

Interface standards  
IEC 60169-12



### Technical Data

#### Electrical Data

Impedance	other $\Omega$
Interface frequency max.	0.2 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0218 kg

#### Environmental Data

Operating temperature	-55 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PSU (Polysulfone)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Crimp ferrule	Brass	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00181587
Catalogue drawing	DCA-00045040
Assembly instruction	DOC-0000201061

### Ordering Information

Single package	11_UHF-0-7-18/033_-E
----------------	----------------------

### Additional Information

Suitable cables	RG_214_/U, GX_07272_D, RADOX_RF_214
-----------------	-------------------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11\\_UHF-0-7-18/033\\_-E](#)