

Coaxial Panel Connector 13_BMA-50-0-13/199_N

Description

Straight panel receptacle plug, flange mount

Interface standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Number of matings	1000
Weight	0.0028 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	

Related Documents

Outline drawing	DOU-00010219
Catalogue drawing	DCA-00010221

Ordering Information

Single package	13_BMA-50-0-13/199_NE
----------------	-----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[13_BMA-50-0-13/199_NE](#)