

Coaxial Cable Connector 14_BMA-50-3-3/199_N

Description

Straight bulkhead cable plug

Interface standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0037 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Stainless Steel	
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Brass	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DCA-00045259
Assembly instruction	DOC-0000185322
Mounting hole	DOU-00008972

Ordering Information

Single package	14_BMA-50-3-3/199_NE
----------------	----------------------

Additional Information

Suitable cables	RG_223_/U, ENVIROFLEX_142, RG_142_B/U
-----------------	---------------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[14_BMA-50-3-3/199_NE](#)