

Coaxial Cable Connector 16_4310-50-5-Y1/003_-

Description

Right angle cable plug

Interface standards
IEC 61169-54



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0267 kg

Environmental Data

Operating temperature	-55 °C to 90 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NBR (Nitrile butadiene rubber)	

Related Documents

Outline drawing	DOU-00259118
Catalogue drawing	DCA-00264976
Assembly instruction	DOC-0000453173

Ordering Information

Bulk 100 pcs package	16_4310-50-5-Y1/003_-H
Single package	16_4310-50-5-Y1/003_-E

Additional Information

Suitable cables	SUCOFORM_250-01_FEP, EZ_250_M17
-----------------	---------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[16_4310-50-5-Y1/003_-H](#)