

## Coaxial Cable Connector 16\_716-50-3-10/003\_M

### Description

Right angle cable plug

Interface standards

IEC 61169-4\_CECC 22190\_DIN 47223\_VG 95250

### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.1091 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00007208
Assembly instruction	DOC-0000181540

### Ordering Information

Single package	16_716-50-3-10/003_ME
----------------	-----------------------

### Additional Information

Suitable cables	RG_223_/U
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

16\_716-50-3-10/003\_ME